




ROCKER SWITCHES

SERIES 4A

• Sub-miniature Rocker switch



AGENCY APPROVALS

File N° E195524

CHARACTERISTICS

- A tiny switch suitable for most miniature equipments.
- High current switching up to 3 Amps @ 120 VAC or 28 VDC.

SPECIFICATIONS

Contact Rating: 5 (silver) - 3A with resistive load @ 120 VAC or 28 VDC - 1.5A with resistive load @ 250 VAC - A (gold) or K* (gold/tin-lead) - 0.4 VA max @ 20 VAC or DC max

Electrical life: 30,000 cycles at full load

Operating Temperature: -30°C to 85°C


Contact Resistance: 20 m Ω max. initial @ 2-4 DVC; 100 mA for both coin silver and gold plated contacts Insulation Resistance: 1000 $M\Omega$ min. Dielectric Strength: 1000 VRMS @ sea level

MATERIALS

Case: Dially phthalate (DAP) Rockers: Nylon

Bushing: Brass, nickel plated Housing: Stainless steel


Terminal/Switch support: 3/4 brass electrotin
























SERIES 4A


TERMINATIONS



















SERIES 4A

TERMINATIONS



Snap-in Terminal Mounting Snap-in Terminal Mounting Snap-in Terminal Mounting H9S **V9**S **U2S** U3S

H95 V95 U25 U35 have the same P.C mounting but with snap-in bracket

CONTACT MATERIALS

CONTACT RATINGS

S Moving Contacts: coin silver, silver plated

Terminals: brass, silver plated

Rating: 3 Amps @ 120 VAC or 28 VDC 1.5 Amps @ 250 VAC

A (std) Moving Contacts: brass with gold plate over nickel plate

Terminals: brass with gold plate over nickel plate Rating: 0.4 Volts/Amps max @ 20 VAC or DC max

G Moving Contacts: coin silver gold plated Terminals: brass silver plated and gold plated

> Note: G option used for either "high" (2 Amps @ 250 VAC) or "low" (0.4 Volts/Amps max) contact rating

(one exclude the other)

K Same as A, but with pre-tinned terminals

PACKAGING

Transparent Trays 15x21x4 cm



Qty per tray: (ST, PC Terminals) Series 4A1x 500 pcs 4A2x 200 pcs

MARKING (on products)

The switches are individually marked with the following information:

Side 1 TRADE MARK SERIES AND MODEL DATE CODE

RATING Side 2 CONTACTS

Note: Not all information may be available on some products.

LABELLING (on packaging)

The label on each tray gives full information on the products contained.



A Bar code indicating Model, Quantity, Date Code enables easy traceability.